

FLAMMABLE MATERIAL STORAGE

Flammable Material Storage Laboratory Refrigerators and Freezers

- Meets NFPA and OSHA guidelines for flammable material storage in general laboratory work areas
- UL Listed
- Temperature Performance:
Refrigerators: 0°C to 10°C, Preset at 4°C
Freezers: -18°C to -25°C, Preset at -20°C
Dual Temp: Refrigerator Preset at 4°C
Freezer Preset at -20°C
- Exterior Adjustable Mechanical Thermostat
- 120 VAC Operation with Power Cord
- Leveling Legs
- Keyed Door Lock
- White Baked on Powder Coat Finish
- Heavy Duty Powder Coated Shelves
- Durable ABS Material Door Liner
- Probe Access Port (3/8")

Accessories

- Caster Platform
- Additional Full Shelf



Flammable Material Storage

LAB Model	Cu. Ft	Defrost	Temp	EXT. Doors	INT. Doors	Shelves	Width	Depth	Height	HP	Amps	Weight
LABH-14-RF	14	Cycle	+4C	1 Solid	0	1 Adj/2 Fixed	32	32	60	1/4	4	226
LABH-14-FF	14	Manual	-20C	1 Solid	0	3 Fixed	32	32	60	1/4	4	223
LABH-17-RF	17	Auto	+4C	1 Solid	0	1 Adj/2 Fixed	32	32	65	1/4	4	254
LABH-17-FF	17	Manual	-20C	1 Solid	0	3 Fixed	32	32	65	1/4	4	251
LABH-20-RF	20	Cycle	+4C	1 Solid	0	1 Adj/3 Fixed	32	34	71	1/4	4	306
LABH-20-FF	20	Manual	-20C	1 Solid	0	4 Fixed	32	34	71	1/4	4	303
LABH-30-RF	30	Cycle	+4C	1 Solid	0	5 Adjustable	35	35	72	1/3	7	359
LABH-30-FF	30	Manual	-20C	1 Solid	0	3 Fixed/2 Adj	35	35	72	1/3	7	356
LABH-30-DTF	30	Manual	+4/-20	1 Solid	1	3 Adj Refrig	35	35	72	1/3	7	374

HAZARDOUS LOCATION



Hazardous Location (Explosion Proof) Laboratory Refrigerators and Freezers

- Meet NFPA and OSHA guidelines for Hazardous Location(s), Class 1, Division II, Group C & D. These units are not intended for use in general clinical or research laboratories.
- UL Listed
- Temperature Performance:
 - Refrigerators: 0°C to 10°C, Preset at 4°C
 - Freezers: -18°C to -25°C, Preset at -20°C
 - Dual Temp: Refrigerator Preset at 4°C
 - Freezer Preset at -20°C
- Exterior Adjustable Mechanical Thermostat sealed in UL Listed Explosion Proof Box
- Unit Must Be Hard Wired in Conduit to 120 VAC Power Source. Power Cords with Plugs are NOT ACCEPTABLE
- Leveling Legs
- Keyed Door Lock
- Stainless Steel Handle (30 cu. ft. Models only)
- White Baked on Powder Coat Finish
- Heavy Duty Powder Coated Shelves
- Durable ABS Material Flat Door Liner
- Probe Access Port (3/8")

Accessories

- Caster Platform
- Additional Full Shelf

Hazardous Location

LAB Model	Cu. Ft	Defrost	Cycle	EXT. Doors	INT. Doors	Shelves	Width	Depth	Height	HP	Amps	Weight
LABH-14-RX	14	Cycle	+4C	1 Solid	0	1 Adj/2 Fixed	32	31	66	1/4	4	238
LABH-14-FX	14	Manual	-20C	1 Solid	0	3 Fixed	32	31	66	1/4	4	235
LABH-17-RX	17	Cycle	+4C	1 Solid	0	1 Adj/2 Fixed	32	31	71	1/4	4	266
LABH-17-FX	17	Manual	-20C	1 Solid	0	3 Fixed	32	31	71	1/4	4	263
LABH-20-RX	20	Cycle	+4C	1 Solid	0	1 Adj/3 Fixed	32	33	77	1/4	4	318
LABH-20-FX	20	Manual	-20C	1 Solid	0	4 Fixed	32	33	77	1/4	4	315
LABH-30-RX	30	Cycle	+4C	1 Solid	0	5 Adjustable	35	34	78	1/3	7	371
LABH-30-FX	30	Manual	-20C	1 Solid	0	3 Fixed/2 Adj	35	34	78	1/3	7	368
LABH-30-DTX	30	Manual	+4/-20	1 Solid	1	3 Adj Refrig	35	34	78	1/3	7	386



www.apexlec.com
1 866 • 522 • 1384